



3D lipo



A Powerful Three Dimensional Alternative to Liposuction

This advanced technology targets **fat removal, cellulite** and **skin tightening** without the need to exercise.

3in1

Cavitation

Cavitation is a natural phenomenon based on low frequency ultrasound. The Ultrasound produces a strong wave of pressure to fat cell membranes. A fat cell membrane cannot withstand this pressure and therefore disintegrates into a liquid state. The result is natural fat loss.

Cellulite

Ultrasound cavitation is widely recognised as one of the most effective cellulite reduction technologies available today. Using specific settings we can effectively target cellulite in addition to the treatment of fat.

Radio Frequency Skin Tightening

Focus Fractional RF is the 3rd generation of RF technology. It utilises three or more pole/electrodes to deliver the RF energy under the skin. This energy is controlled and limited to the treatment area. Key advantages of this technology are high treatment efficacy, no pain as less energy is required, shorter treatment services and variable depths of penetration.



60cm treatment area



After 8 Treatments



Unlike most Lipo devices the client is **not required to exercise** post treatment.

For more information or an on site demonstration please call **1300 335 476 / 1300 3DLIPO.**

Cavitation

What is cavitation?


Ultrasound cavitation is widely recognised as one of the most effective cellulite reduction and local fat loss technologies available today.

Cavitation is body sculpting with no anaesthesia, no scars, no discomfort, no downtime and presents a risk free alternative to liposuction.

Cavitation is a natural phenomenon based on low frequency ultrasound. The Ultrasound produces a strong wave of pressure to fat cell membranes. A fat cell membrane cannot withstand this pressure and therefore disintegrates into a liquid state. The result is natural fat loss.

What happens to the released fat?

After disruption of adipose's cellular membrane the fat in the form of triglycerides is released into the interstitial space between the cells, where they are enzymatically metabolised to glycerol and free fatty acids. Water soluble glycerol is absorbed by the circulatory system and used as the energy source whereas the insoluble free fatty acids are transported to the liver and processed as fatty acids from food.



Radio Frequency Skin Tightening

Why Fractional Focus Rf Technology?

Fractional Focus RF is the 3rd generation RF technology. It uses multi polar/electrodes to deliver the RF energy into skin. It is combined with Red Photodynamic energy to optimize the results.




- Skin Tightening & Lifting & Skin Rejuvenation

The Focus Fractional RF energy penetrates the skin layers to selectively heat the skin tissue and the extra cellular matrix where the collagen fibres are embedded. The local heating causes an immediate contraction of collagen fibres, and at the same time increases the metabolism of the fibroblasts thereby accelerating the production of new collagen and elastin fibres.

The concentration of collagen fibres and the regeneration of the collagen and elastin deposits, tighten the skin layers creating a smoother, healthier and younger looking skin.

- Body Contouring & Cellulite

Focus Fractional RF technology selectively increases the temperature of fat cells doing so simultaneously in deep and superficial layers of fat. This increases the metabolism and release of liquid fat from fat cells. Normal cells can support 60°C but fat cells start to be melted at 41°C. After treatment and release of liquid fat, the fat cells shrink in size and skin is restored closer to its original form, reducing or eliminating the cellulite appearance.



A Powerful **New** Dimension in **Non-Surgical** Fat Removal

For more information call: **1300 335 476 / 1300 3DLIPO**

Specification

Cavitation

Frequency: 32Khz +10%
Power: Max 200W
Transducer: 2 Flat and 2 Focus
Max Treat Area: 60CM²

Radio Frequency

Frequency: 10.0Mhz
Absorbed Power: 50W
Output Power: 45W
Power Input: AC 110/220V,
50/60Hz

General

Program: Pre-set and Manual Selection
Display: 5.6" colour touch screen
Treatment Time: From 5-30min
Power Supply: 110V-120V/220V-240V, 50/60Hz
Warranty: 12 months (main frame)
Mark: CE